

HUBBELL Premise Wiring

Fiber Optic Adapter, SC/APC Simplex, 8- Port, Loaded with 8 Adapters

By Hubbell Premise Wiring
Catalog # [FSPNSCA8](#)



Features

-
-
-

Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Simplex, APC
Catalog Number	FSPNSCA8
Color	Green
Environmental Conditions	Indoor
Item Type	SC Simplex, APC
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Repeatability	0.1 dB
Service Life	500 matings
Single/Multimode	SM
Sub Brand	OptiChannel

Temperature Rating	-40C to +85C
UPC	662620340210

Electrical Ratings

Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog Page - PREM G11 Catalog Page](#)
[Catalog Page - PREM G9 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Engineering Drawing - PREMISE_HWS14978C_ACAD](#)
[Literature - FIBERHUBB N-Series Fiber Panels](#)
[Sales Drawings - PREMISE_HWS14978C_SALESDRAWING](#)
[Specifications - FSPNSCA8](#)