

Fiber Optic Panel Adapter, 12-Fiber,
SC Simplex, 12-Port, Loaded with 12
Adapters, Zircon Sleeves, Blue

By Hubbell Premise Wiring
Catalog # [FSPNSCSS12](#)



Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Simplex
Catalog Number	FSPNSCSS12
Color	Blue
Environmental Conditions	Indoor
Item Type	SC Simplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Size	5.1" X 1.1"
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620340418

Electrical Ratings

Insertion Loss 0.30 dB

Conductor Related

Fiber Size 125 Micron
Fiber Type Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Catalog Page - PREM G11 Catalog Page](#)
[Catalog Page - PREM G9 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Engineering Drawing - PREMISE_HWS14974C_ACAD](#)
[Literature - FIBERHUBB N-Series Fiber Panels](#)
[Sales Drawings - PREMISE_HWS14974C_SALESDRAWING](#)
[Specifications - FSPNSCSS12](#)