

HUBBELL

Premise Wiring

PlugTrak, Aluminum, Tamper Resistant, 20A125V, 3' Length, Anodized



By Hubbell Premise Wiring
Catalog # [HBLALU24GB306TR](#)

PlugTrak, Tamper Resistant, 20A125V, 3', Anodized

Features

- Tamper Resistant
- Available in 3ft. 5 ft. or 6 ft. lengths
- Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions
- Multiple spacing configurations
- Hubbell designed and manufactured 15 or 20 Amp receptacles

General

Catalog Number	HBLALU24GB306TR
EU RoHS Indicator	Contact Manufacturer
Number of Receptacles	6
Series	Aluminum
Style	Tamper Resistant
Type	Single Circuit
UPC	783585453095

Dimensions

Length	3 ft
--------	------

Electrical Ratings

Current / Amperage Rating	20 A
---------------------------	------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog Page - WDK S-36 Catalog Page](#)
[Catalog Page - PREM U37 CatalogPage](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Premise Wiring Catalog](#)