



PlugTrak, Aluminum, Tamper Resistant, 20A125V, 5' Length, Anodized

By Hubbell Premise Wiring
Catalog # [HBLALU24GB512TR](#)



PlugTrak, Tamper Resistant, 20A125V, 5', Anodized

Features

- Tamper Resistant
- Available in 3ft, 5 ft, or 6 ft. lengths
- Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions
- Multiple spacing configurations
- Hubbell designed and manufactured 15 or 20 Amp receptacles

General

EU RoHS Indicator	Contact Manufacturer
Number Of Receptacles	5
Style	Tamper Resistant
Type	Single Circuit
UPC	783585453101

Dimensions

Length 5 ft

Electrical Ratings

Current / Amperage Rating 20 A

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - PREM S37 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-HBLALU24GB512TR-SPEC-EN | REV 7/2023