



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Gray

By Hubbell Premise Wiring
Catalog # [HC5EGY01](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Gray

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620234939

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	Meets And Exceeds ANSI/TIA
----------------------	----------------------------

Product Assets

[Literature - SPEEDGAIN Category 5e Enhanced Performance System](#)
[Sales Drawings - HC5EGY - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-HC5EGY01-SPEC-EN | REV 7/2023