

HUBBELL

Premise Wiring

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Orange

By Hubbell Premise Wiring
Catalog # [HC5EOR01](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Orange

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC5EOR01
Color	Orange
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category Type 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620235165

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Literature - SPEEDGAIN Category 5e Enhanced Performance System](#)

[Sales Drawings - HC5EOR - PDF](#)



A Hubbell brand