



Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 100' Length, Blue

By Hubbell Premise Wiring
Catalog # [HC6AB100](#)



Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 100'
Length, Blue

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Color	Blue
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620229171

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Literature - SPEEDCHANNEL Ascent Category 6A UTP Cable](#)
[Literature - NEXTSPEED® Ascent 10GbE Cable](#)
[Sales Drawings - HC6AB1 - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-HC6AB100-SPEC-EN | REV 7/2023