

HUBBELL

Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 15' Length, Gray

By Hubbell Premise Wiring
Catalog # [HC6AGY15](#)



Ascent Patch Cord Cat 6A Slim, 15'

General

Application	Category 6A
Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6AGY15
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620229928

Dimensions

Outside Diameter	0.218
------------------	-------

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalog Page - PREM D3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - NEXTSPEED® Ascent 10GbE Cable](#)
- [Literature - SPEEDCHANNEL Ascent Category 6A UTP Cable](#)
- [Literature - Catch the Wi-Fi 6 Wave](#)
- [Sales Drawings - HPW_HC6AGY_DRAWING_PDF](#)



A Hubbell brand