



# Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 20' Length, Gray

By Hubbell Premise Wiring  
Catalog # [HC6AGY20](#)



Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 20' Length, Gray

## Application

Category 6A

## General

Attenuation	.1dB
Boot Type	PVC
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620229935

## Dimensions

Outside Diameter	0.218
------------------	-------

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Product Assets

[Catalog Page - PREM D3 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Literature - SPEEDCHANNEL Ascent Category 6A UTP Cable](#)  
[Literature - NEXTSPEED® Ascent 10GbE Cable](#)  
[Literature - Catch the Wi-Fi 6 Wave](#)  
[Sales Drawings - HPW\\_HC6AGY\\_DRAWING\\_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-HC6AGY20-SPEC-EN | REV 7/2023