

HCC Full Size Data Cabinet, 42U H X
32 in W X 40 in D in white

By Hubbell Premise Wiring
Catalog # [HCC423240WH](#)

Data Cabinet, 42U H X 32 in W X 40 in D in white



*Representative Image

Features

- Depth adjustable 19" vertical mounting rails with easy to read depth marking. U numbers printed on 19" rails.
- Contoured mesh front door and split rear door with over 80% perforation for superior airflow.
- Front and rear doors are lockable.
- Lockable split sidewalls for easy 1 person access to the equipment.
- Fan kit and other accessories are also available to complete your solution.

Application

Premise

Performance

- Static Load Capacity - 3,000 lbs
- Mesh door - 80% airflow
- Equipment mounting - Supports 19" wide rack mount equipment
- 1 RU cabinet filler panel in black, flat - MCCBP175
- 2 RU Cabinet filler panel in black,flat - MCCBP350
- On rail 19" grounding busbar kit, tin plated, single pack - HGRKTHT
- On rail 19" grounding busbar kit, tin plated, 10 pack - HGRKTHT10

General

Catalog Number	HCC423240WH
Color	Black
Compatibility	EIA 310
Frame	Sheet steel
Material	Sheet steel
Mounting Type	Leveling feet

Series
Specifications

HCC Full Size Cabinet

- Rack Spaces - 42
- Finish - Durable textured powdered coating
- Sidewalls - Locking Split
- Cable Access - Top with rectangular removable plate and grommet

Vented doors with top, sidewalls and 19" mounting rails

Full size IT cabinet

662620376776

Style

Type
UPC

Dimensions

Cubic Capacity	103754.7 cu.in
Depth	43 in
Height	76.6 in
Width	31.5 in

Conductor Related

Cable Entry	Through Top
-------------	-------------

Certifications And Compliance

Industry Standard(s)	UL 2416, EIA 310
Nema Rating	None

Logistics

Carton Quantity	50
Pallet Quantity	2700

Product Assets

[Sales Drawings - HWS15383C](#)
[Specifications - HCC423240WH](#)