

HUBBELL

Premise Wiring

By Hubbell Premise Wiring
Catalog # [HFCD1002R4](#)



Features

-
-
-
-

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Riser
Catalog Number	HFCD1002R4
Color	Aqua
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.17 (4.4) • Cable Weight (lb/kft) - 12 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer

Sub Brand	Fiber Optics
Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620555508

Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	2

Certifications And Compliance

Industry Standard(s)	TIA
----------------------	-----

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Specifications - HFCD1002R4](#)