

HUBBELL

Premise Wiring

By Hubbell Premise Wiring
Catalog # [HFCD1002RS](#)



Features

-
-
-
-

Application

Data Tranmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Riser
Catalog Number	HFCD1002RS
Color	Yellow
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.17 (4.4) • Cable Weight (lb/kft) - 12 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics

Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620555522

Electrical Ratings

Wavelength	1310/1550 Nanometers
------------	----------------------

Conductor Related

Fiber Size	Single Mode
Fiber Type	OS2, SM
Number of Fibers	2

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Industry Standard(s)	TIA

Product Assets

[Catalog Page - PREM I03 Catalog Page](#)
[Catalog Page - PREM I3 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD1002RS](#)