

HFCD14 Series Indoor/Outdoor Tight Buffer, 2 strand, I/O Tight Buffer Plenum, OM3, MM, Black Jacket

By Hubbell Premise Wiring

Catalog # [HFCD14002P3BK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 2 strand, I/O Tight Buffer Plenum, OM3, MM , Black Jacket

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

Specifications

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-4 • Telcordia GR-409 and GR-20 • TIA-568.3-D
----------------------	---

Conductor

Fiber Size	OM3
Fiber Type	OM3, MM
Number Of Fibers	2

Current

Wavelength	850/1300 Nanometers
------------	---------------------

General

Sub Brand	Fiber Optics
Type	Cable
Cable Rating	I/O Tight Buffer Plenum
Material - Jacket	PVC
UPC	662620555539
Color	Black

Operational

Attenuation	3.5/1.5 Db per Kilometer
Temperature Rating	0 Degrees C to 70 Degrees C
Bandwidth	2000 bps

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)

