

HUBBELL
Premise Wiring

HFCD14 Series Indoor/Outdoor Tight Buffer, 72 strand, I/O Tight Buffer Riser, OM4, MM, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD14072R4BK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 72 strand, I/O Tight Buffer Riser, OM4, MM , Black Jacket

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission


Specifications

Industry Standard(s) TIA

Conductor

Fiber Size OM4
Fiber Type OM4, MM
Number Of Fibers 72

Current



Wavelength 850/1300 Nanometers

General

Sub Brand Fiber Optics
Type Cable
Cable Rating I/O Tight Buffer Riser
Material - Jacket PVC
UPC 662620555775
Color Black

Operational

Attenuation 3.5/1.5 Db per Kilometer
Temperature Rating -20 Degrees C to 70 Degrees C
Bandwidth 4000 bps

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)