

HFCD15 Series Indoor Tight Buffer
Distribution, 6 strand, Plenum,
Armored, OS2, SM, Yellow Jacket

By Hubbell Premise Wiring
Catalog # [HFCD15006PS](#)

HFCD15 Series Indoor Tight Buffer Distribution, 6 strand, Plenum,
Armored, OS2, SM , Yellow Jacket.



Application

Data Tranmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Plenum, Armored
Catalog Number	HFCD15006PS
Color	Yellow
Material - Jacket	PVC
Specifications	• Armor - Aluminum Interlock • Cable Diameter in (mm) - 0.63 (16) • Cable Weight (lb/kft) - 165 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332109

Electrical Ratings

Wavelength	1310/1550 Nanometers
------------	----------------------

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number of Fibers	6

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Specifications - HFCD15006PS](#)