

HFCD15 Series Indoor Tight Buffer
Distribution, 24 strand, Plenum,
Armored, OM4, MM, Aqua Jacket

By Hubbell Premise Wiring
Catalog # [HFCD15024P4](#)



Features

-
-
-
-

Application

Data Tranmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Plenum, Armored
Catalog Number	HFCD15024P4
Color	Aqua
Material - Jacket	PVC
Specifications	• Armor - Aluminum Interlock • Cable Diameter in (mm) - 0.69 (17.4) • Cable Weight (lb/kft) - 188 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable

UPC 662620332147

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	24

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - OptiChannel HFCD15 Series Indoor Armored Distribution Fiber Cable](#)
- [Literature - Quick Turn Custom Fiber Trunk Assemblies Program](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Literature - Cut to Length Fiber Cable](#)
- [Specifications - HFCD15024P4](#)