

# HUBBELL Premise Wiring

## HFCD15 Series Indoor Tight Buffer Distribution, 72 strand, Riser, Armored, OM4, MM , Aqua Jacket

By Hubbell Premise Wiring  
Catalog # [HFCD15072R4](#)

HFCD15 Series Indoor Tight Buffer Distribution, 72 strand, Riser,  
Armored, OM4, MM , Aqua Jacket.

### Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Durable Aluminum Interlock Armor
- Premium Fiber For Enhanced Optical Performance

### Application

Data Transmission

### General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Riser, Armored
Catalog Number	HFCD15072R4
Color	Aqua
Sub Brand	Fiber Optics
Temperature Rating	-10 Degrees C to 70 Degrees C
Type	Cable
UPC	662620343389



**Oh No!**  
IMAGE COMING SOON

### Electrical Ratings

Wavelength 850/1300 Nanometers

### Conductor Related

Fiber Size OM4  
Fiber Type OM4, MM  
Number of Fibers 72

### Certifications And Compliance

Industry Standard(s)

- ANSI/ICEA S-83-596
- NFPA-262/UL910/CSA FT-4
- Telcordia GR-409
- TIA-568.3-D

### Product Assets

[Literature - Fiber Optic Cable Guide](#)  
[Specifications - HFCD15072R4](#)