

HFCD19 Series Indoor/Outdoor
Tight Buffer, 24 strand, Plenum,
Armored, OS2, SM, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD19024PSBK](#)

HFCD19 Series Indoor/Outdoor Tight Buffer, 24 strand, Plenum,
Armored, OS2, SM , Black Jacket.

Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Multi-Purpose Outdoor Duct To Building Riser Application
- Premium Fiber For Enhanced Optical Performance

Application

Data Tranmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Plenum, Armored
Catalog Number	HFCD19024PSBK
Color	Black
Material - Jacket	PVC
Specifications	• Armor - Aluminum Interlock • Cable Diameter in (mm) - 0.69 (17.4) • Cable Weight (lb/kft) - 188 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics



Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332369

Electrical Ratings

Wavelength	1310/1550 Nanometers
------------	----------------------

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number of Fibers	24

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Product Assets

[Catalog Page - PREM I04 Catalog Page](#)
[Catalog Page - PREM I4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD19024PSBK](#)