

HFCH5 Series - Outdoor Loose
Tube, 48 strand, OM3, MM, OSP,
Armored Double Jacket, Outdoor
Loose Tube, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCH5048BK3](#)



HFCH5 Series - Outdoor Loose Tube, 48 strand, OM3, MM, OSP,
Armored Double Jacket, Outdoor Loose Tube, Black.

Features

- Multimode Bend-Insensitive Optical Fiber
- TIA-598-C Colored Buffer Tubes
- Gel-Free Water Blocking Construction
- Robust Design For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	2000 bps
Cable Rating	OSP, Armored Double Jacket
Catalog Number	HFCH5048BK3
Color	Black
Material - Jacket	MDPE
Specifications	<ul style="list-style-type: none">• Armor - Corrugated Steel• Cable Diameter in (mm) - 0.54 (13.8)• Cable Weight (lb/kft) - 112• Construction - Armored Double Jacket Loose Tube, 6F/Tube, Central Strength Member

Sub Brand
Temperature Rating
Type
UPC

- Fiber Coating - 250 Micron Acrylate Buffer
- Fiber Optics
-40 Degrees C to 75 Degrees C
Cable
662620606057

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

Fiber Size	OM3
Fiber Type	OM3, MM
Number of Fibers	48

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/ICEA S-87-640• ANSI/TIA-758-A• Telcordia GR-20• TIA-568.3-D
----------------------	---

Product Assets

[Sell Sheets - FIBERHUBB HFCH5 Series Outdoor Armored Double Jacket Loose Tube Fiber Cable](#)
[Specifications - HFCH5048BK3](#)