

HFCH6 Series Indoor/Outdoor
Loose Tube 6 strand, Riser,
Armored, OM4, MM , Black Jacket.

By Hubbell Premise Wiring
Catalog # [HFCH6006R4BK](#)

HFCH6 Series Indoor/Outdoor Loose Tube 6 strand, Riser,
Armored, OM4, MM , Black Jacket.

Features

- Multimode Bend-Insensitive Optical Fiber
- Loose Tube
- Durable Aluminum Interlock Armor
- Indoor/Outdoor
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Riser, Armored
Catalog Number	HFCH6006R4BK
Color	Black
Sub Brand	Fiber Optics
Temperature Rating	-40 Degrees C to 70 Degrees C
Type	Cable
UPC	662620342689



Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	6

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

[Sell Sheets - Premise_PLSSCAF010_SellSheet](#)
[Specifications - HFCH6006R4BK](#)