

HI-IMPACT Adapter, Fiber, LC,  
Multimode, Bulkhead

By Hubbell Premise Wiring  
Catalog # [HIBLCM](#)



HI-IMPACT Adapter, Fiber, LC, Multimode, Bulkhead

Features

- IP68 water immersion and dust protection for harsh environments
- Chemical resistance and superior 100lb pull force
- Wide range of operational temperature -40C/70C
- Low insertion loss and exceeding ODVA requirements
- Factory tested with bayonet style locking mechanism

Application

Data Transmission

General

Catalog Number	HIBLCM
Color	Black
Series	HI-IMPACT
Style	IP68
Sub Brand	FiberHubb

Temperature Rating	(-)40 Degrees C to 70 Degrees C
Type	Fiber
UPC	662620371610

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• IP68</li><li>• Telcordia GR-409</li><li>• TIA-568.3-D</li></ul>
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Literature - Secure your network with Hi Impact fiber cords and assemblies](#)  
[Sales Drawings - HWS15292C](#)  
[Specifications - HIBLCM](#)