

HUBBELL Premise Wiring

Cabinet Components, QUADCAB 24" H x 24" D, Window Door, Black

By Hubbell Premise Wiring
Catalog # [HQC2424](#)

Cabinet Components, QUADCAB 24" H x 24" D, Window Door, Black



*Representative Image

Features

- Standard Plexiglass door
- Adjustable depth mounting rails w/threaded #12-24 holes
- Symmetrical design for reversible door swing
- Rectangular knock-out in base, for ease of terminated cable retrofits
- Fan knockouts for easy of installation

Application

Premise data

General

Catalog Number	HQC2424
Color	Black
Item Type	Wall Mounted Enclosures
Material	Steel, Cold Rolled
Material - Mounting Hardware	Standard
Series	<ul style="list-style-type: none">• QUADCAB• HQC
Style	Swing Out

Type
UPC

Wall Mount
662620370354

Dimensions

Cubic Capacity	13017.6 cu.in
Depth	24 in
Height	24 in
Thickness	0.0781
Width	22.6 in

Certifications And Compliance

Industry Standard(s)	EIA/ECA-310-E Universal Mounting Pattern
----------------------	--

Product Assets

[Catalog Page - PREM N04 Catalog Page](#)
[Installation Manuals - HWS772286_Installation manual](#)
[Literature - QUADCAB® HQC Series Wall-Mount Cabinets](#)
[Sales Drawings - HWS15274C](#)
[Specifications - HQC2424](#)