



Hubbell Premise Wiring

Snap-In, F Coax, Nickel, Gray

By Hubbell Premise Wiring
Catalog # [NSF70GY](#)

Snap-In, F Coax, Nickel, Gray



Application

CATV

General

| | |
|------------------------------|---|
| Contact | Phosphor Bronze |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 1) Nickel F-Coax Connector |
| Material - Mounting Hardware | Screw Mounting |
| OEM Brand Name | Hubbell Premise Wiring |
| Style | Coupler |
| Temperature Rating | Max Continuous- 75 Degrees C, Minimum- -40 Without Impact |
| Type | F-Type |
| UPC | 883778503306 |

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|--------------------|------------------|
| Connectivity | Female to Female |
| Contact Resistance | Per TIA |
| Insertion Loss | Per TIA |

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - PREM V10 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Sales Drawings - HPW_NSF70_DRAWING_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-NSF70GY-SPEC-EN | REV 7/2023