



Hubbell Premise Wiring

LGX Max Series CS Cassette, 36 Port, 18 Duplex CS to 3 MTP, OM3/OM4, Aqua

By Hubbell Premise Wiring
Catalog # [OCCSM34](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 36 CS to 3 MTP, OM3/OM4, Aqua

Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Easy Access Pull Tab for Quick Disconnect

Application

Interconnect

General

| | |
|--------------------------|--------------|
| Enclosure Type | LGX |
| Environmental Conditions | Indoor |
| Number Of Ports | 18 |
| UPC | 662620343877 |

Dimensions

| | |
|--------------|-------------|
| Display Size | 4.0" x 1.1" |
| Height | 1.1 in |

Electrical Ratings

| | |
|--------------|----------|
| Connectivity | Cassette |
|--------------|----------|

Conductor Related

| | |
|------------------|---------|
| Fiber Type | OM3/OM4 |
| Number Of Fibers | 36 |

Certifications and Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS |
|----------------------|---|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Literature - LGX Max CS and SN Cassettes](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-OCCSM34-SPEC-EN | REV 7/2023