



# LGX Max Series CS Cassette, 36 Port, 18 Duplex CS to 3 MTP, OS2, Blue

By Hubbell Premise Wiring  
Catalog # [OCCSSM](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 36 CS to 3 MTP, OS2, Blue

### Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Easy Access Pull Tab for Quick Disconnect

### Application

Interconnect

### General

Enclosure Type	LGX
Environmental Conditions	Indoor
Number Of Ports	18
UPC	662620343860

### Dimensions

Display Size	4.0" x 1.1"
Height	1.1 in

### Electrical Ratings

Connectivity	Cassette
--------------	----------

### Conductor Related

Fiber Type	OS2
Number of Fibers	36

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Telcordia GR-326-CORE</li><li>• TIA-568-C.3</li><li>• TIA-604-FOCIS</li></ul>
----------------------	---

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalog Page - PREM A7 CatalogPage](#)  
[Catalog Page - PREM G7 CatalogPage](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - LGX Max CS and SN Cassettes](#)



A proud member of the Hubbell Family.