

Fiber LGX Cassette, OM1, LC Duplex
to MTP, Beige

By Hubbell Premise Wiring
Catalog # [OCLC62](#)



Features

-
-
-

Application

Interconnect

Performance

Optical - Total insertion loss - Less than 1.5dB (test data included)

General

Catalog Number	OCLC62
Color	Beige
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	LC Duplex to MTP
Material	Ceramic
Material - Mounting Hardware	Snap-In
OEM Brand Name	Hubbell Premise Wiring
Repeatability	0.1 dB
Service Life	500 matings
Specifications	• Cassette Type - LC Duplex 12F • Dimensions - 5.1" H x 1.1" W x 2.75" D • Fiber Type - 62.5QM, OM1 • Housing material - 16ga powder coated steel • MTP connector - 12-fiber male receptacle on back side • Sleeve material - Ceramic

Style	LC Duplex 12F
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620844794

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Cassette
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	250 Micron
Fiber Type	OM1

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM G5 CatalogPage](#)
[Catalog Page - PREM G05 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - OCLC62 - PDF](#)
[Specifications - PREMISE_OCLC62_spec](#)
[Specifications - OCLC62](#)