

Fiber High Density Cassette, , LC
Duplex to MTP, Aqua

By Hubbell Premise Wiring
Catalog # [OCLCHD50G4](#)



Features

- OM2 Fiber
- 12-Fiber Strands
- OM4 Fiber.

Application

Interconnect

General

Catalog Number	OCLCHD50G4
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	LC Duplex to MTP
Material - Mounting Hardware	Snap-In
OEM Brand Name	Hubbell Premise Wiring
Repeatability	0.1 dB
Service Life	500 matings
Style	Ultra Compact
Temperature Rating	0C to 70C
UPC	662620228471

Dimensions

Display Size5.1" X 1.1"

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size125 Micron

Logistics

Carton Quantity25

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM A8 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Sales Drawings - OCLCHD - PDF](#)
- [Sell Sheets - FIBERHUBB Ultra Compact Fiber LC to MPO Cassette Modules](#)
- [Sell Sheets - FIBERHUBB High Density 144 Port 1U Fiber Enclosure](#)
- [Specifications - OCLCHD50G4](#)