

Fiber LGX Cassette, OM4, LC Quad
to MTP, Violet

By Hubbell Premise Wiring
Catalog # [OCLCQ50G4CVI](#)



Features

-
-
-

Application

Interconnect

Performance

Optical - Total insertion loss - Less than 1.5dB (test data included)

General

Catalog Number	OCLCQ50G4CVI
Color	Violet
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	LC Quad to 2 MTP
Material	Ceramic
Material - Mounting Hardware	Snap-In
Repeatability	0.1 dB
Service Life	500 matings
Style	LC Quad 24F
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620607740

Dimensions

Display Size5.1" X 1.1"

Electrical Ratings

Connectivity	Cassette
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	250 Micron
Fiber Type	OM4

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM G06 Catalog Page](#)
[Catalog Page - PREM G6 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - OCLCQ50G4CVI](#)
[Specifications - PREMISE_OCLCQ50G4CVI_spec](#)