



LGX Max Series SN Cassette, 72 Port, 36 Duplex SN to 6 MTP, OM3/OM4, Aqua

By Hubbell Premise Wiring
Catalog # [OCSNM34](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 72 SN to 6 MTP, OM3/OM4, Aqua

Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Push-Pull on Boot for Quick Connect/Disconnect

Application

Interconnect

General

Enclosure Type	LGX
Environmental Conditions	Indoor
Number Of Ports	36
UPC	662620343853

Dimensions

Display Size	4.0" x 1.1"
Height	1.1 in

Electrical Ratings

Connectivity	Cassette
--------------	----------

Conductor Related

Fiber Type	OM3/OM4
Number of Fibers	72

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Telcordia GR-326-CORE• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM A7 CatalogPage](#)
[Catalog Page - PREM G7 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - LGX Max CS and SN Cassettes](#)



A proud member of the Hubbell Family.