



LGX Max Series SN Cassette, 72 Port, 36 Duplex SN to 6 MTP, OS2, Blue

By Hubbell Premise Wiring
Catalog # [OCSNSM](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 72 SN to 6 MTP, OS2, Blue

Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Push-Pull on Boot for Quick Connect/Disconnect

Application

Interconnect

General

| | |
|--------------------------|--------------|
| Enclosure Type | LGX |
| Environmental Conditions | Indoor |
| Number Of Ports | 36 |
| UPC | 662620343846 |

Dimensions

| | |
|--------------|-------------|
| Display Size | 4.0" x 1.1" |
| Height | 1.1 in |

Electrical Ratings

| | |
|--------------|----------|
| Connectivity | Cassette |
|--------------|----------|

Conductor Related

| | |
|------------------|-----|
| Fiber Type | OS2 |
| Number of Fibers | 72 |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• Telcordia GR-326-CORE• TIA-568-C.3• TIA-604-FOCIS |
|----------------------|---|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Catalog Page - PREM A7 CatalogPage](#)
[Catalog Page - PREM G7 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - LGX Max CS and SN Cassettes](#)



A proud member of the Hubbell Family.