



Hubbell Premise Wiring

# LGX Max Series SN Cassette, 72 Port, 36 Duplex SN to 6 MTP, OS2, Blue

By Hubbell Premise Wiring  
Catalog # [OCSNSM](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 72 SN to 6 MTP, OS2, Blue

## Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Push-Pull on Boot for Quick Connect/Disconnect

## Application

Interconnect

## General

Enclosure Type	LGX
Environmental Conditions	Indoor
Number Of Ports	36
UPC	662620343846

## Dimensions

Display Size	4.0" x 1.1"
Height	1.1 in

## Electrical Ratings

Connectivity	Cassette
--------------	----------

## Conductor Related

Fiber Type	OS2
Number Of Fibers	72

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Telcordia GR-326-CORE</li> <li>• TIA-568-C.3</li> <li>• TIA-604-FOCIS</li> </ul>
----------------------	---

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

[Literature - LGX Max CS and SN Cassettes](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-OCSNSM-SPEC-EN | REV 7/2023