

Fiber LGX Cassette, OM2, ST Duplex
to MTP, Black

By Hubbell Premise Wiring
Catalog # [OCST50](#)

Fiber Accessory, Plug and Play Cassette, ST-Style, Multi Mode
50.



Features

-
-
-

Application

Interconnect

Performance

Optical - Total insertion loss - Less than 1.5dB (test data
included)

General

Catalog Number	OCST50
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor
Item Type	ST Duplex to MTP
Material	Ceramic
Material - Mounting Hardware	Snap-In
OEM Brand Name	Hubbell Premise Wiring
Repeatability	0.1 dB
Service Life	500 matings
Specifications	• Cassette Type - ST-Style • Dimensions - 5.1" H x 1.1" W x 2.75" D • Fiber Type - 50QM, OM2 • Housing material - 16ga powder coated steel • MTP connector - 12-fiber male receptacle on back side • Sleeve material - Ceramic

Style	ST-Style
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620844848

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Cassette
Insertion Loss	0.75 dB Max
Return Loss	55

Conductor Related

Fiber Size	250 Micron
Fiber Type	OM2

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM G6 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - OCST - PDF](#)
[Specifications - OCST50](#)
[Specifications - PREMISE_OCST50_spec](#)