



# Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Blue, 55' Length

By Hubbell Premise Wiring  
Catalog # [PC6AB55](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Blue, 55' Length

## Application

Category 6A

## General

Attenuation	.1dB
Boot Type	PVC
Color	Blue
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620215228

## Dimensions

Outside Diameter 0.218

## Electrical Ratings

Voltage Rating 300V AC kV

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Product Assets

[Sales Drawings - PC6AB - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-PC6AB55-SPEC-EN | REV 7/2023