



Hubbell Premise Wiring

Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Black, 60' Length

By Hubbell Premise Wiring
Catalog # [PC6ABK60](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Black, 60' Length

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Color	Black
EU RoHS Indicator	No
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620215341

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Literature - NEXTSPEED® Cat 6A Ascent Jacks](#)
[Sales Drawings - PC6AB - PDF](#)



A proud member of the Hubbell Family.