

Copper Solutions, Patch Cord,
Cat6A, 10GHz, Shielded, Green, 7'
Length

By Hubbell Premise Wiring
Catalog # [PC6AGN07](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Green, 7'
Length

Features

- Cat6A
- 10GHz
- Shielded
- Green
- 7' Length

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	PC6AGN07
Color	Green
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA

UPC662620204369

Dimensions

Outside Diameter0.218

Electrical Ratings

Voltage Rating300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

Logistics

Carton Quantity100

Product Assets

[Catalog Page - PREM D04](#) [Catalog Page](#)
[Catalog Page - PREM D4](#) [CatalogPage](#)
[Catalogs - Premise Wiring](#) [Catalog](#)
[Literature - NEXTSPEED® Cat 6A Ascent Jacks](#)
[Specifications - PC6AGN07](#)