

HUBBELL

Premise Wiring

Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Red, 3' Length

By Hubbell Premise Wiring
Catalog # [PC6AR03](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Red, 3' Length

Application

Category 6A

General

| | |
|-----------------------|---|
| Attenuation | .1dB |
| Boot Type | PVC |
| Color | Red |
| EU RoHS Indicator | Yes |
| Item Type | NEXTSPEED Ascent Shielded Category 6A Patch Cords |
| Material - Insulation | Flame Redardant PVC |
| Material - Jacket | Flame Redardant PVC |
| OEM Brand Name | Hubbell Premise Wiring |
| Plug Type | RJ45 |
| Temperature Rating | Per TIA |
| UPC | 662620204208 |

Dimensions

| | |
|------------------|-------|
| Outside Diameter | 0.218 |
|------------------|-------|

Electrical Ratings

| | |
|----------------|------------|
| Voltage Rating | 300V AC kV |
|----------------|------------|

Conductor Related

| | |
|----------------------|-------------|
| Conductor Stranding | Stranded |
| Conductor Type | Copper |
| Number of Conductors | 8-Conductor |
| Wire Size | #24 AWG |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 200 |
|-----------------|-----|

Product Assets

[Catalog Page - PREM D4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
PREM-PC6AR03-SPEC-EN | REV 6/2024