



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Red, 20' Length

By Hubbell Premise Wiring
Catalog # [PC6AR20](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Red, 20' Length

Application

Category 6A

General

Attenuation	.1dB
Boot Type	PVC
Color	Red
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620204253

Dimensions

Outside Diameter	0.218
------------------	-------

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM D4 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-PC6AR20-SPEC-EN | REV 7/2023