



# Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, White, 10' Length

By Hubbell Premise Wiring  
Catalog # [PC6AW10](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, White, 10' Length

## Application

Category 6A

## General

Attenuation	.1dB
Boot Type	PVC
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620204444

## Dimensions

Outside Diameter	0.218
------------------	-------

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Logistics

Carton Quantity	90
-----------------	----

## Product Assets

[Catalog Page - PREM D4 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Sales Drawings - HPW\\_PC6AW\\_DRAWING\\_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-PC6AW10-SPEC-EN | REV 7/2023