



Hubbell Premise Wiring

# Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, White, 20' Length

By Hubbell Premise Wiring  
Catalog # [PC6AW20](#)



Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, White, 20' Length

## Application

Category 6A

## General

Attenuation	.1dB
Boot Type	PVC
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Ascent Shielded Category 6A Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620204475

## Dimensions

Outside Diameter	0.218
------------------	-------

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

- [Catalog Page - PREM D4 Catalog Page](#)
- [Catalogs - HPW CATALOG\\_2023\\_FULL](#)
- [Sales Drawings - HPW\\_PC6AW\\_DRAWING\\_PDF](#)



A proud member of the Hubbell Family.