



Copper Solutions, Patch Cords, Cat6, Shielded, Blue, 15' Length

By Hubbell Premise Wiring
Catalog # [PS6B15](#)



Copper Solutions, Patch Cords, Cat6, Shielded, Blue, 15'
Length

Application

Data Transmission

General

Attenuation	.1dB
Boot Type	Strain Relief
Color	Blue
Plug Type	RJ45
Sub Brand	Copper Patch Cords
Temperature Rating	Per TIA
Type	Cat6, PS6
UPC	662620604626

Dimensions

Length	15 ft
Outside Diameter	0.218 in

Electrical Ratings

Voltage Rating	300 VAC
----------------	---------

Conductor Related

Conductor Stranding	Solid
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	UL1863
----------------------	--------

Product Assets

[Sales Drawings - HPW_PS6B_DRAWING_PDF](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
PREM-PS6B15-SPEC-EN | REV 1/2024