

HUBBELL

Premise Wiring

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 5', 15A 125V, 1-Circuit, Tamper Resistant



By Hubbell Premise Wiring
Catalog # [PT155112TR](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 5', 15A 125V, 1-Circuit, Tamper Resistant

Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

Performance

Electrical - Crush Resistance - 300 lbs., Electrical - Impact Resistance - 5 ft. lbs, Electrical - Receptacle Rating - NEMA 5-15R & 5-20R, Environmental - Flame Rating - UL94V-0, Environmental - Temperature Range - -25.6° to 158° F, Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
----------------------	---

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	5
-----------------------	---

Current

Voltage Rating	125 VAC
Current / Amperage Rating	15 A

Dimensions

Weight	2.1 lb.
Length	5 ft

General

Specifications	• Material - UV Stabilized PVC • Number of Receptacles - 5 Duplex • PlugTrak Amperage - 15A • PlugTrak Length - 5 Foot • Receptacle Face - Thermoplastic • Spacing - 12 Inch
Color	Office White
Style	Tamper Resistant
Product Family	Non-Metallic
UPC	783585455952
Type	Single Circuit
Item Type	Pre-Wired PlugTrak

Logistics

Pallet Quantity	550
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)