



Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 1-Circuit, 3) Duplex



By Hubbell Premise Wiring
Catalog # [PT206124](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 1-Circuit, 3) Duplex

Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

General

Color	<ul style="list-style-type: none">• Office White• Blanc cassé
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	3
Performance	<ul style="list-style-type: none">• Electrical - Crush Resistance - 300 lbs.• Electrical - Impact Resistance - 5 ft. lbs• Electrical - Receptacle Rating - NEMA 5-15R & 5-20R• Environmental - Flame Rating - UL94V-0• Environmental - Temperature Range - -25.6° to 158° F• Mechanical - Wire - #12 AWG Stranded Copper
Type	<ul style="list-style-type: none">• Single Circuit• Single Circuit
UPC	783585091167

Dimensions

Length 6 ft

Electrical Ratings

Current / Amperage Rating 20 A
Voltage Rating 125 VAC

Conductor Related

Wire Size #12 AWG THHN

Certifications and Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E118895 / E119190
- UL Standard UL 5A

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - PREM S63 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-PT206124-SPEC-EN | REV 7/2023