

HUBBELL

Premise Wiring

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 2-Circuit, 3) Duplex

By Hubbell Premise Wiring
Catalog # [PT206224](#)



Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 2-Circuit, 3) Duplex

Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

General

Catalog Number	PT206224
Color	Office White
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	3
Performance	Electrical - Crush Resistance - 300 lbs. Electrical - Impact Resistance - 5 ft. lbs Electrical - Receptacle Rating - NEMA 5-15R & 5-20R Environmental - Flame Rating - UL94V-0 Environmental - Temperature Range - -25.6° to 158° F Mechanical - Wire - #12 AWG Stranded Copper
Series	Non-Metallic
Style	Standard
Type	Two Circuits
UPC	783585091211

Dimensions

Length	6 ft
--------	------

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications And Compliance

Industry Standard(s)	CSA Standard C22.2 no. 62 E118895 / E119190 UL Standard UL 5A
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - PREM U63 CatalogPage](#)
- [Catalog Page - WDK S-62 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Premise Wiring Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PREM-PT206224-SPEC-EN | REV 6/2024