



2" Tough Floor Fitting

By Hubbell Premise Wiring
Catalog # [PT27A](#)

Fire-Rated Poke-Through Pedestal Series, 2" Tough Floor Fitting



Application

Through Floor Fitting

General

EU RoHS Indicator	No
Item Type	Through Floor Fitting
Material	Composite
Performance	<ul style="list-style-type: none">Electrical - Power Wiring Capacity - Up to ten #12 AWG type THHN wires, or Up to six #12 AWG and two #10 AWG type THHN wiresElectrical - Voice/Data Wiring Capacity - Up to two 25 pair tel./data cables (100 #22 AWG tel./data conductors), or Up to two IBM Type 2 data cablesMechanical - Max. Cu Cross Section - 1/2" Power EMT .0461 sq. in., 3/4" Low Voltage EMT .0500 sq. in.Mechanical - UL Spacing Restrictions - Min. of 2 ft. O.C. and not more than one unit per each 65 sq. ft. of floor area in each span
Style	Through-Floor Fittings
UPC	783585076157

Dimensions

Display Size Standard Sized Product

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">Fire Resistance - R8429Outlet Box- E31999
----------------------	--

Product Assets

Related Products

- [FR680GYA - Pedestal, 6-Gang, Gray](#)
- [FR280GYA - Pedestal, 2-Gang, Gray](#)
- [FR480BKA - Pedestal, 4-Gang, Black](#)
- [FR280BKA - Pedestal, 2-Gang, Black](#)
- [FR480GYA - Pedestal, 4-Gang, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-PT27A-SPEC-EN | REV 7/2023