



## Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Brass Finish

By Hubbell Premise Wiring  
Catalog # [PT7IGFSDBRSA](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush Duplex Series, Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Brass Finish

### Features

- Complete 3" Fire-Rated Poke-Through
- Prewired 20A IG Duplex Receptacle
- (2) 1/2" Diameter Holes for Low Voltage Wiring
- Non-metallic Cover with Painted Aluminum Flange
- Includes Junction Box

### General

Application - For Use On	Carpet
EU RoHS Indicator	No
Finish Type	Brass
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex IG Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Style	FRPT - Complete Kits
UPC	783585494234



### Certifications and Compliance

- |                      |                       |
|----------------------|-----------------------|
| Industry Standard(s) | • cULus Listed        |
|                      | • Meets ADA Standards |
|                      | • UL 514A Listed      |

### Product Assets

[Customer Notices - Prop 65 Notice](#)

### Related Products

[BRS2RCA - Brass Replacement Cover](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-PT7IGFSDBRSA-SPEC-EN | REV 7/2023