

Complete Unit With 20A IG Duplex,
(2) 1/2" Diameter Holes for Low
Voltage Wiring, Ivory

By Hubbell Premise Wiring
Catalog # [PT7IGFSDIA](#)



In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush
Duplex Series, Complete Unit With 20A IG Duplex, (2) 1/2"
Diameter Holes for Low Voltage Wiring, Ivory

General

Application - For Use On	Carpet
Catalog Number	PT7IGFSDIA
EU RoHS Indicator	No
Finish Type	Ivory
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex IG Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Specifications	<ul style="list-style-type: none">Cover Material - Thermoplastic cover with aluminum flange

Style	FRPT - Complete Kits
UPC	783585494210
	<ul style="list-style-type: none">Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8)Mounting - 3 in. (76.2) cored concrete diameter through hole

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">cULus ListedMeets ADA StandardsUL 514A Listed
----------------------	---

Product Assets

[Catalog Page - WDK P-32 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - PT7IGFSDIA](#)