

15A Kitchen Counter Receptacle,
Surface Mount, Nickel

By Hubbell Premise Wiring
Catalog # [RCT200NI](#)

15A Kitchen Counter Receptacle, Surface Mount, Nickel

Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

General

Catalog Number	RCT200NI
Color	Nickel
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2
Series	Countertop Receptacle
Style	Surface
Type	Power Only
UPC	883778307966

Dimensions

Dimensions	4.20 in x 4.20 in x 6.48 in
Height	6.48 in
Length	4.2 in
Width	4.2 in

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	630

Product Assets

- [360 Product View - BRYA_RCT200NI](#)
- [3D Product View - BRYA_RCT200NI](#)
- [Catalog Page - WDK Z-25 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Multifamily Property Tech Enhancements](#)
- [Literature - Residential Catalog](#)
- [Literature - Property Management | Home Enhancements | Innovation and Convenience](#)
- [Specifications - RCT200NI](#)
- [Video - Hubbell Tri-Power Pop-Up Receptacle](#)

