



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Gray

By Hubbell Premise Wiring
Catalog # [RJ650GYTR](#)



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle,
Cat 6 Jack, F Coax, Decorator Frame, Gray

Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none">• Gray• Gris
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302473

Dimensions

Display Size 1-Gang Standard Sized

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - PREM R48 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-RJ650GYTR-SPEC-EN | REV 7/2023