



# J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory

By Hubbell Premise Wiring  
Catalog # [RJ650ITR](#)



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle,  
Cat 6 Jack, F Coax, Decorator Frame, Ivory

## Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

## Application

Ideal for flat panels TVs

## General

Color	<ul style="list-style-type: none"><li>• Ivory</li><li>• Ivoire</li></ul>
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302480

## Dimensions

Display Size 1-Gang Standard Sized

## Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - PREM R48 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-RJ650ITR-SPEC-EN | REV 7/2023