



Recessed 4" Series, Kit

By Hubbell Premise Wiring
Catalog # [S1R4PTNKL](#)

Fire Rated Poke Throughs, Recessed 4" Series, Through Floor Fitting, Satin Nickel Plated Cover, S1FRPTJB, No Subplate



Features

- For use with a 4.00" to 4.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

4" Fire-Rated Poke-Through Series

General

Accessory Type	4" FRPT Kit
Application - For Use On	Concrete
Color	Nickel
EU RoHS Indicator	Contact Manufacturer
Finish Type	Satin Nickel Plated Cover
Item Type	4" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	4" Core Hole
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	4" Recessed Rated Poke Through Kits
UPC	783585446127

Conductor Related

Cable Entry Through Cover

Certifications and Compliance

- Industry Standard(s)
- cULus Listed
 - Meets ADA Standards
 - UL 514A Listed

Product Assets

[Catalog Page - PREM R39 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

Related Products

[S1R4SP2X2DUPLEX - 4" Series, Sub Plate, \(1\) Duplex Opening, \(2\) Keystone Jack Openings](#)
[S1R4PPT - 4" Pre-Pour Tube](#)
[S1R4SPSIMPLEX - 4" Series, Sub Plate, \(1\) 1.40" Opening](#)
[S1R4SPTWIST - 4" Series, Sub Plate, \(1\) 1.60" Opening](#)
[S1R4SPDUPLEX - 4" Series, Sub Plate, \(1\) Duplex Opening](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-S1R4PTNKL-SPEC-EN | REV 7/2023